




带自闭阀的特殊吸板 PY2E 和 P2Y2E，章鱼式系统专用

本页所述的吸板与上文所述的PY和P2Y一样，区别在于每个吸孔内均设有自闭阀。若提取物体缺失或泡沫橡胶抓取面有缺陷时，自闭阀会自动关闭抽气，从而防止其余吸孔或正常抓持吸盘的真空度下降。

与带校准孔的章鱼式系统相比，此特性可降低真空发生器的流量，从而起到节能的作用。这些吸板也可以安装在任何位置上，而不会改变其操作特性。



型号	吸力 Kg	A	B	C Ø	D Ø	E	F	G	H	阀门 数量	仅橡胶 型号	重量 Kg
PY2E 20 30	75.4	200	300	40	---	17	15	18	32	24	Y 20 30	1.26
PY2E 20 40	100.5	200	400	40	---	17	15	18	32	32	Y 20 40	1.71
PY2E 20 60	150.8	200	600	40	---	17	15	18	32	48	Y 20 60	2.62
PY2E 30 30	113.0	300	300	40	---	17	15	18	32	36	Y 30 30	1.99
PY2E 30 40	150.8	300	400	40	---	17	15	18	32	48	Y 30 40	2.61
PY2E 30 50	188.4	300	500	40	---	17	15	18	32	60	Y 30 50	3.24
PY2E 40 40	201.0	400	400	40	---	17	15	18	32	64	Y 40 40	3.42
PY2E 40 60	301.5	400	600	40	---	17	15	18	32	96	Y 40 60	5.27
PY2E 40 100	502.4	400	1000	40	---	17	15	18	32	160	Y 40 100	8.70
PY2E 60 80	602.9	600	800	40	---	17	15	18	32	192	Y 60 80	10.45
PY2E 60 120	904.4	600	1200	40	---	17	15	18	32	288	Y 60 120	15.77
PY2E 80 100	1037.3	800	1000	40	---	17	15	18	32	320	Y 80 100	17.64
PY2E D0 35	100.5	---	---	40	350	17	15	18	32	32	Y D0 35	1.89
PY2E D0 50	213.5	---	---	40	500	17	15	18	32	76	Y D0 50	3.76
P2Y2E 20 30	75.4	200	300	40	---	17	30	18	47	24	2Y 20 30	1.33
P2Y2E 20 40	100.5	200	400	40	---	17	30	18	47	32	2Y 20 40	1.79
P2Y2E 20 60	150.8	200	600	40	---	17	30	18	47	48	2Y 20 60	2.65
P2Y2E 30 30	113.0	300	300	40	---	17	30	18	47	36	2Y 30 30	2.02
P2Y2E 30 40	150.8	300	400	40	---	17	30	18	47	48	2Y 30 40	2.64
P2Y2E 30 50	188.4	300	500	40	---	17	30	18	47	60	2Y 30 50	3.30
P2Y2E 40 40	201.0	400	400	40	---	17	30	18	47	64	2Y 40 40	3.57
P2Y2E 40 60	301.5	400	600	40	---	17	30	18	47	96	2Y 40 60	5.37
P2Y2E 40 100	502.4	400	1000	40	---	17	30	18	47	160	2Y 40 100	9.00
P2Y2E 60 80	602.9	600	800	40	---	17	30	18	47	192	2Y 60 80	10.85
P2Y2E 60 120	904.4	600	1200	40	---	17	30	18	47	288	2Y 60 120	16.36
P2Y2E 80 100	1037.3	800	1000	40	---	17	30	18	47	320	2Y 80 100	18.21
P2Y2E D0 35	100.5	---	---	40	350	17	30	18	47	32	2Y D0 35	2.03
P2Y2E D0 50	213.5	---	---	40	500	17	30	18	47	76	2Y D0 50	3.88

